ROTARY DRILLING AND VIBRATOR, MUD DELIVERY AND CEMENT HOSES GRADE E



HIGH PRESSURE OILFIELD HOSE

APPLICATION

Flexible connection between standpipe and top drive/swivel or between pump and standpipe for pumping mud at extra high pressure in oil drilling and exploration work.

TEMPERATURE	(-25°C to +100°C) (-13°F to +212°F)							
CONSTRUCTION	Tube	Black Nitrile Rubber						
	Reinforcement	Multiple layers of textile fabric and steel cable						
	Cover	PCR						
STANDARDS	API 7K 6th Edition FSL1 and FSL2, ISO 47693, ABS Type Approvals							
COUPLINGS	Crimped(FSL1) and Bonded(FSL2)							

ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
3	76	5.6	142	517	7500	1290	18750	47.2	1.2	34.7	76.5	62	203.4	AP03E	765
3 1/2	89	6.0	152	517	7500	1290	18750	55.1	1.4	39.2	86.4	62	203.4	AP35E	889
4	102	7.4	187	517	7500	1290	18750	59.1	1.5	52.0	114.6	62	203.4	AP04E	921
5	127	8.3	211	517	7500	1290	18750	70.9	1.8	72.0	158.7	62	203.4	AP05E	922

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.